



Micro™ Auto CPAP

Item#
CAPSOM505000-KIT

Transcend Micro offers the full-featured CPAP performance you want every day in a clean, simple and sophisticated design. The future of CPAP therapy is available now!



Features & Benefits

- Small:** About the size of a baseball
- Lightweight:** Weighs less than a mobile phone
- Works with any CPAP mask:** Use your existing mask
- Quiet operation:** The Transcend WhisperSoft™ muffler is included

Smallest and lightest travel CPAP device

Weighing less than 0.5 lbs. and measuring less than 4 inches wide, the Transcend Micro is the most portable CPAP currently available on the market.

Compatible with any CPAP Mask

The Transcend Micro is compatible with any CPAP mask. Simply connect your mask to the provided Transcend Micro Airflex 6-foot hose. Shorter or longer Transcend Micro AirFlex hoses are also available.

Unplug and sleep anywhere with more power options

The Transcend Micro comes with an AC (wall) power adapter for use at home, at your cabin, or at a hotel. The Transcend PowerAway™ P8 portable battery is an ideal option for camping, flights, or travel to remote locations off the grid. The battery doubles as a backup power source during power outages.

Adjustable GentleRise and AirRelief technology

The Transcend Micro features the GentleRise technology to help you fall asleep more comfortably by delivering a lower pressure when you turn on the device and go to bed. It then gradually increases pressure over time until you reach the desired level. Plus, it's adjustable, so you can fine-tune your ramp times or turn off the ramp feature altogether to ensure you're getting the restful sleep you deserve.

The Transcend Micro is also designed with the AirRelief feature to help you breathe easier and more comfortably while you sleep by reducing pressure on exhalation.

Stay dry, all the time

The Transcend Micro's convenient drying mode removes excess moisture from your mask and tubing. When you wake up in the morning, simply activate the 30-minute drying cycle to start a steady stream of air moving through the hose and mask. The drying mode will help ensure you have a dry mask waiting for you when it's time to go to bed.

What's Included

- Transcend Micro CPAP
- Transcend Micro AirFlex™ 6-foot hose
- Transcend WhisperSoft™ Muffler Kit
- Transcend travel pouch
- AC power adapter
- 2 Year manufacturer's warranty



Specifications

Warranty	2 years
Therapy Mode	Auto
Product Dimensions (in.)	3.6 in x 3.6" x 2.4" (9.1 cm x 9.1 cm x 6.1 cm)
Product Weight (lbs.)	0.48 lbs (219.5g)
Power	AC Input: 100-240VAC, 50-60Hz Power Supply Output: 18VDC, 1.67 Amp
Battery Option	Transcend PowerAway P8 Battery: 14.4 VDC, 5,200 mAh
Air Relief	Yes
Operating Pressure Range	4-20 cmH2O
GentleRise Ramp Duration	0-45 mins
Operating Temperature Range	41 to 95°F (5 to 35°C)
Auto Altitude Adjustment (up to 8,000 ft)	Yes
Sound Level	27 dBA*
Compliance Data	Yes
Bluetooth Capability	Yes

*Sound pressure level reported in a typical use environment



To order or for more information

P 312.997.9980 E sales@sunsethcs.com W SUNSETHCS.COM

